

# Ultra range

High-efficiency water softener range utilising our unique sof'n'polish system for ultra-soft water. Suitable for all types of homes. If you need help choosing the right model, please call our expert team on 01986 784759.



Model	H x W x D (mm)	People	Daily capacity (litres @ 300 ppm)	Salt tablet use per regen (kg)	Max flow rate (lpm)	Water pressure (bar)	Operating temp (°C)
Ultra HE	557 x 269 x 489	1 - 10	1,520	0.61 - 1.2	65	1.5 - 5	2 - 49
Premio HE	788 x 269 x 489	2 - 20	3,040	1.22 - 2.4 (tablet only)	61	1.5 - 5	2 - 49

If using Ultraflow hoses for 28mm applications please allow an extra 10mm to width. Family size is based on allowing 142 litres per person per day and water hardness of 300ppm. (Source: Energy Savings Trust)

3/4" mbsp connections. Electrical supply – 220v 3 pin plug with plug-in transformer

\*Upon registration & servicing as recommended by Monarch Water



## Key features

- Sof'n'polish system - double the contact time for ultra soft water
- WRAS approved - demonstrating quality and durability of the highest standard
- Leading 7 year parts and 2 year labour warranty (upon registration and servicing as recommended by Monarch Water)
- Opti-brining with HE resin - only regenerates the resin (food grade) that has been used
- Built in customer protect programme (CPP) that a) detects leaks in your plumbing system b) delays regeneration until 2am c) learns your water usage patterns to regenerate accordingly and make substantial savings on salt and water use d) automatically adjusts to BST and GMT time changes
- High flow rates with low pressure drops
- Free flow valve technology - flow rates up to 65 lpm
- Ultra HE can use tablet or block sat. Premio HE uses tablet salt only.
- Complete with full standard installation kit and water hardness test kit
- Robust design for quick and easy installation
- Comes with Monarch Water's unique Rapid-fit bypass, reducing components needed for installation by up to 80%



Rapid-fit  
bypass



Tablet salt for Ultra HE  
& Premio HE



Block salt can be used  
for Ultra HE only

